

SENTRY[®] II

MULTI-SENSOR THERMAL IMAGING SYSTEM
WITH PROGRAMMABLE PAN/TILT



APPLICATIONS

- FORWARD AREA LINE OF DEFENSE
- FORCE PROTECTION
- BORDER SECURITY
- COASTAL SURVEILLANCE
- TRAINING RANGES

FEATURES

- High-sensitivity long wave thermal sensor
- 5/20 degree dual field of view optics
- Auto focus on both sensors
- Daylight camera
- Advanced image processing
- Portable
- Built in test (BIT)
- Autoscan multiple programmable presets and slew-to-cue other network sensors
- Rugged, sealed, continuous 360° pan/tilt enclosure with optional heaters and protective stow position

It's all FLIR inside

BENEFITS

- Clear imagery in total darkness, through smoke, fog, and most obscurants
- Detect man size targets at 3 km
- Sharp imagery between zoom settings reduces operator workload
- Powerful, sensitive camera offers excellent zoom and color quality
- Sharp thermal imagery regardless of scene dynamics
- Configured to be a field transportable system for fast deployment
- Intelligent self test confirms that the system is operating optimally
- Autonomous operation with slaving to other longer range sensors; integrates easily into networks utilizing MPEG videos and full remote control
- Hundreds of SENTRY systems fielded with USAF in harsh desert and arctic climates
- FLIR controls the entire supply chain on the critical technology inside ThermoVision systems ensuring fast service and long term support



Crisp thermal imagery



Powerful daylight/low light camera



SENTRY® II

THERMAL IMAGING PERFORMANCE

Sensor type	320 x 240 long wave VOx microbolometer
Number of fields of view	2
Wide FOV	20° x 15°
Narrow FOV	5° x 3.75°
E-zoom	1x to 4x continuous
Image processing	STACE™ (digital image enhancement), Histogram Equalization (HEQ)
Palletes	Black, white, rainbow, iron (+ inverted)
Spectral band	7.5-13 μm
Automatic features	Focus, image optimization, temperature compensated focus, defrosting system

DAYLIGHT IMAGING PERFORMANCE

Sensor type	0.25 in. CCD
Optical zoom	(18x) 48° to 2.7° continuous
E-zoom	12x, continuous
Lines of resolution	460 television lines NTSC, 470 television lines PAL
Automatic features	Auto focus, advanced image processing enhancements

SYSTEM FEATURES

Programmable search	Program multiple preset scene locations
Remote power control	On/off power save feature
Automatic heater	Separate power supply supports arctic climate use
Built in Test (BIT)	Intelligent self diagnostics tests vital functions
Pelco D® compliance	Supports Pelco D® communication protocol

PAN/TILT SPECIFICATIONS

Az range	n x 360°
El range	-35° to +60°
Slew rate	Pan 0-120°/sec

VIDEO OUTPUTS

Video	NTSC (RS-170) or PAL (CCIR)
Connector types	BNC (2) provides thermal and daylight video simultaneously
Optional MPEG video	Requires optional embedded network feature

POWER

Power requirements	18-32 VDC
Power consumption	35 W (average)

ENVIRONMENTAL

IP rating	IP65
Operating temp	-32°C to 55°C (-26°F to 131°F)

DIMENSIONS, WEIGHTS AND MOUNTING

Dimensions	397 x 300 x 226 mm (16" x 11" x 9")
Weight	21 kg (46.3 lb.)

INTERFACES

Command and Control (all functions)	RS 232 or RS 485
Ethernet (optional)	Command and Control and MPEG videos (2)
Pelco D®	Compliant

STACE™
Digital Image Enhancement

Equipment described herein may require US Government authorization for export purposes. Diversion contrary to US law is prohibited. ©2010 FLIR Systems, Inc. Specifications are subject to change. Check website: www.flir.com/GS_06012010



CORPORATE HEADQUARTERS

FLIR Systems, Inc.
27700 SW Parkway Ave.
Wilsonville, OR 97070
PH: +1 800.727.3547

BOSTON

FLIR Systems, Inc.
25 Esquire Road
North Billerica, MA 01862
PH: +1 800.464.6372

HUNTSVILLE

FLIR Systems, Inc.
Huntsville, AL USA
PH: +1 256.325.3547

PITTSBURGH

FLIR Systems, Inc.
Freeport, PA USA
PH: +1.724.295.2880

WASHINGTON, D.C.

FLIR Systems, Inc.
2800 Crystal Drive, Suite 330
Arlington, VA 22202 USA
PH: +1 703.416.6666

EUROPE

FLIR Systems Ltd.
West Malling, Kent
United Kingdom
PH: +44.1732.220011

CANADA

FLIR Systems Ltd.
Burlington, ON
Canada
PH: +1 800.613.0507

SWEDEN

FLIR Systems AB
Täby, Sweden
PH: +46.8.753.2500

MIDDLE EAST

FLIR Systems Middle East, FZCO
Dubai Airport Free Zone
PH: +9714.299.6898

www.flir.com/GS

