

Recon[®] B9-FO

MEDIUM RANGE, LIGHTWEIGHT
THERMAL BIOCULAR



APPLICATIONS

TARGET ACQUISITION
FORWARD OBSERVATION
RECONNAISSANCE
SURVEILLANCE
SITUATIONAL AWARENESS
FORCE PROTECTION
BORDER PATROL

FEATURES

High resolution, large format 640x480 longwave VOx Microbolometer

New automatic digital image processing techniques

Lightweight and rugged MIL-STD-810F qualified

Internal digital magnetic compass and GPS

Continuous zoom color camera

Flexible, power, and video options

Integrated Laser Range Finder (LRF)

Laser pointer (option)

It's all FLIR inside

BENEFITS

Delivers unmatched range performance and image quality

Offers image detail unmatched by analog systems

Reduces operator fatigue for long duration missions without sacrificing field hardening

Allows operator to determine target location and communicate direction to support personnel

Provides color discrimination to operator, improving the ability to describe a daylight scene

Can be configured for tripod use for continuous operation with video output

Accurate rangefinding to >3Km

Offers additional tactical advantage when coupled with night vision equipment; has eyesafe training operation mode

FLIR controls the entire supply chain on the critical technology inside Recon systems, ensuring fast service and long term support



High sensitivity thermal imagery



Split screen mode viewing capability



Recon[®] B9-FO

THERMAL IMAGING PERFORMANCE

Sensor type	640 x 480 VOx microbolometer
FOV	9.3° h x 7° v (320 x 240 VOx option)
Digital zoom	Continuous to 4x
Spectral band	8-12 μm
Automatic features	AGC, STACE™ Digital Detail Enhancement (DDE), Auto focus

VISIBLE COLOR CHANNEL

Sensor type	1/4" HAD CCD
Pixel format	768 x 494 pixels
Optical zoom	Continuous to 10x
Digital zoom	Continuous to 4x
Sensitivity	0.1 lux
FOV	9.3° h x 7° v, optical zoom from 46° to 4.6°

SYSTEM FEATURES

Global Positioning System (GPS)	C/A code (supports military GPS plug-in)
Digital Magnetic Compass	360° Az, +/- 90° El, 0.2° resolution
Integrated Eyesafe Laser Rangefinder (LRF)	1.54 μm, > 3 km, Class IM
Laser Pointer (LP) Option	852nm, Class 3B, 0.5/30mW
Image Presentation	Monochrome, color and split screen (picture over picture)

POWER

Power requirements	7 VDC/ 11 W (9 V to 32 VDC external)
Battery type and life	Qty 2 long life rechargeable D cell Lithium batteries >5.0 hours continuous and >6.0 hours in power save mode

ENVIRONMENTAL

Mil-Spec	MIL-STD-810F
Operating temp	-32°C to +55°C (-26°F to +131°F)

DIMENSIONS, WEIGHT & MOUNTING

Dimensions	22.1 x 21.3 x 10.9 cm (8.7" x 8.4" x 4.3")
Weight	<2.5 kg (5.5 lb.), batteries included
Mounting	Tripod mount 1/4-20 base

INTERFACES

Command and Control	RS 232/422
Image Download	USB (stores up to 1000 JPEGs)

STANDARD PACKAGE

Storage/transport case	Hard shell, lockable with fitted foam insert
Adapter/charger	110 VAC/220VAC power supply
Batteries	6 each, Lithium D cells, rechargeable
Lens cleaning kit	Complete cleaning kit in nylon pouch
Cables	Video cable, 3 m with BNC connectors, cigarette lighter, 3m USB cable
Battery charger	110 VAC/220 VAC input
Soft case	Lightweight with padded zippered compartments
Manual	Operator's Manual and Quick Reference Guide

OPTIONS & ACCESSORIES

150 mW LP, Class 3B, 830nm, tripod, display, interface and power cables, soft carry bag

STACE™
Digital Image Enhancement

Equipment described herein may require US Government authorization for export purposes. Diversion contrary to US law is prohibited. ©2011 FLIR Systems, Inc. Specifications are subject to change. Check website: www.flir.com/GS 03302011



CORPORATE HEADQUARTERS

FLIR Systems, Inc.
27700 SW Parkway Ave.
Wilsonville, OR 97070
PH: +1 800.727.3547

BOSTON

FLIR Systems, Inc.
25 Esquire Road
North Billerica, MA 01862
PH: +1 800.464.6372

HUNTSVILLE

FLIR Systems, Inc.
Huntsville, AL USA
PH: +1 256.325.3547

PITTSBURGH

FLIR Systems, Inc.
Freeport, PA USA
PH: +1.724.295.2880

WASHINGTON, D.C.

FLIR Systems, Inc.
2800 Crystal Drive, Suite 330
Arlington, VA 22202 USA
PH: +1 703.416.6666

EUROPE

FLIR Systems Ltd.
West Malling, Kent
United Kingdom
PH: +44.1732.220011

CANADA

FLIR Systems Ltd.
Burlington, ON
Canada
PH: +1 800.613.0507

SWEDEN

FLIR Systems AB
Täby, Sweden
PH: +46.8.753.2500

MIDDLE EAST

FLIR Systems Middle East, FZCO
Dubai Airport Free Zone
PH: +9714.299.6898

www.flir.com/GS



FLIR[®]
Extraordinary Protection